

MULTI FUNCTIONAL HANDPIECES

LARGE	Abdomen, Back and Thigh
MEDIUM	Arm and Calf
SMALL	Face and Neck

SYSTEM SPECIFICATIONS

Radio Frequency	0.8 Mhz
Power	70 W
Vacuum	200 mmHg
LED Wavelength	640/460 nm
Rating	100-240 V, 50/60 Hz
Weight	7.2 kg
Dimension	320 (D) x 405 (W) x 155 (H) mm



RIDM Technology

SAS Technology

Dynamic Pulsation with Minimal Noise

Customized Smart Upgrade


FTB012016

Body Shaping

Cellulite Reduction

Facial Lifting & Tightening

Wrinkle Reduction



Cluederm™ LIFTING PATCH | BODY PATCH



Entire Beauty Solution
Cluederm™

info@cluederm.com | www.cluederm.com

Images and texts are intellectual property of Cluederm. Copying of this material can be subject to charges of both civil and criminal law of legal justice.
Copyright to Cluederm © 2016

دفتر مرکزی: تهران، سهروردی شمالی، بین هوپزه و سرمد، پلاک ۵۰۴، واحد ۱، تلفن: ۸۸۸۶۲۲۳۱، ۸۸۸۶۲۲۱۷

Feel the Rhythm

Refit.™

Smart Facial Rejuvenation and Body Shaping System



شفا تجهیزات
WWW.SHAFATAJHIZ.IR

Cluederm™
Entire Beauty Solution

Feel the Rhythm


Refit™

Smart Facial Rejuvenation
and Body Shaping System



• RIDM (Redesign integrated Dynamic Movement) Technology

Assisted by RIDM technology, various kinds of smart auto programs are operated automatically during whole procedure of treatment without touching the interface and eliminated operator fatigue.



• SAS (Safe Anti-Spark) Technology


Precise output control technology safely protects patient's skin from frequent sparking while delivering high RF energy. This allows aestheticians to use high energy levels without fear.



Brilliant user-centered technology for easier operation and overall treatment result.

• Integrated Technology

Ideal combinations of multi-polar RF, Vacuum suction, and LED technology comfortably achieve a toned, contoured and well shaped body through a non-invasive treatment. This well-combined system brings immediate visible results from the 1st treatment with patient comfort.



Multi-polar RF

The RF energy delivers thermal energy into dermal and deep fatty layer and promotes metabolism, tightens collagen fibers and improves skin elasticity.

Vacuum Suction


Vacuum suction increases blood circulation, reduces viscosity of fat cell clusters and reshape the body. It also helps energy delivery to deeper level of the skin and body.

LED

Optimum wavelength of 640 nm and 460 nm works to circulation and skin tone improvement.

• Dynamic Pulsation with Minimal Noise

Various kinds of powerful pulsation maximizes its drainage effects with minimal noise level.



• Various sizes of Handpieces

3 sizes (large, medium, small) of the handpieces are provided to operate on the face and the body.



• Application

Abdomen



Thigh



Arm



Face

